



LIZOTTE WHOLE MUSSEL SORTER

SPECIFICATIONS

Rate up to 35 pieces per second

Inspects for:

- Cracked shell
- Broken Shell
- Loose Shell
- Hole in Shell
- Mussel filled with sand, rock, or mud
- Empty mussel
- Undersized mussel

Uses non-destructive soft x-ray technology

Mussels are fed randomly on a wide belt

Robust wash-down stainless steel construction

Ejection uses air blasts that are non-damaging to product

Independent of product size and orientation

Operation is from the front panel touch screen

Can be coupled with color camera technology in order to inspect for byssus and barnacles

The Lizotte Whole Mussel Sorter uses soft x-ray technology to inspect mussels in the shell. It process up to 35 pieces per second ensuring that defects are automatically removed from the processing line and only top quality product is sent to market.



GOOD



DEFECT

This system is fully washable and ready for wash-down.



WE CUSTOM BUILD